

#### FRAUNHOFER INSTITUTE FOR MICROELECTRONIC CIRCUITS AND SYSTEMS IMS



1 ToF Camera from TriDiCam GmbH.

## TOF IMAGE SENSORS

# Fraunhofer Institute for Microelectronic Circuits and Systems IMS

Finkenstr. 61
D - 47057 Duisburg
Phone +49 203 37 83-0
Fax +49 203 37 83-266
www.ims.fraunhofer.de

Contact
Michael Bollerott
Phone +49 203 37 83-227
vertrieb@ims.fraunhofer.de

The new Fraunhofer IMS SQCIF image sensor generation for scannerless, real-time, pulse-modulated time-of-flight range imaging cameras is employing a novel high-speed low-noise photodetector. It ensures high precision range measurement at harsh environmental conditions.

The SQCIF PM ToF image sensor is offering a very high degree of flexibility to the user. The sensor enables for instance variable pulse accumulation count settings to improve the precision and increase the dynamic range. The key feature, here, is that these multiple accumulations are realized in the charge domain within the photodetector, hence reducing kTC noise significantly. The sensor can operate with a variety of active light sources and diverse timing. However, it is recommended using the patented MSI scheme since it provides better ambient light suppression.

Linearization within a certain measurement range allows to yield the range information from the output signals by means of the simple formula

$$z = \frac{cT_{shutter}}{2} \frac{V_2 - V_3}{V_1 + V_2 - 2V_3}$$


which can be easily implemented. Usage of intelligent algorithms though allow to increase the measurement range significantly.

The dedicated ToF image sensors enable a multitude of applications in areas as:

- Industrial Imaging
- Machine Vision & Robotic
- Automotive
- Consumer Electronics
- Security and Surveillance







### **Exemplary PM ToF Camera**

Field-of-view 6° x 4,5°

Active light source 75W, 905 nm LASER module,

8 kHz repetition rate, 45 ns pulse width

Measurement range  $\leq 2 \,\mathrm{m}$ 

Achieved precision  $\leq \sigma = 4 \text{ cm}$ ;

 $\leq \sigma/\Delta z = 2 \% @ R = 20 \%;$ 

10 % systematic error

for  $z \le 150 \, \text{cm}$ 

@ accumulation count: 1000

### **Specifications**

Resolution SQCIF (128  $\times$  96) Pixel pitch 40  $\times$  40  $\mu$ m² Package CQFJ84

Measurement range adjustable

Frame rate up to 50 fps
Accumulation count adjustable

Short-time integration window  $\geq 30 \, \text{ns}$ 

Camera gain 0,14 DN/e<sup>-</sup>

Responsivity (@ 525 nm) 6 mDN/ph/pix


Linearity error according to EMVA1288 1,4 % Read noise 700  $\mu$ V

Full-well capacity 250 ke<sup>-</sup>
SNRmax 54 dB
Optical dynamic range 70 dB
Linear output voltage swing 2 V
DSNU according to EMVA1288 2200 e<sup>-</sup>

PRNU according to EMVA1288 1,1 %

Dark current @ 28 °C ≤ 10 000 e<sup>-</sup>/s





- 2 ToF Image Sensor.
- 3 Gray Scale Image.
- 4 Depth Image.